



尖端的真空设备  
铂杉产品选型手册

姓名:夏目

微信:boshanxiamu

电话:185-6656-3069

邮箱:xiamu@boshanvac.com

网址:www.boshanvac.com

地址:东莞市寮步镇寮步坑口桃苑4巷8号

营业联系



# XDD1干式隔膜泵



XDD1隔膜泵体积紧凑高效，用于为小型复合涡轮分子泵在清洁、高真空应用中提供后备，同时也设计为独立台式单元。使用XDD1为小型涡轮分子泵提供支持时，典型的极限压力可达 $5 \times 10^{-8}$ 毫巴以上。XDD1泵用于非侵略性、安全区域应用。

24 V版本设计为提供完整的泵浦系统，可与Edwards涡轮增压器和仪表控制器配合使用。直流电压电机通过15针DIN连接器以24V运行。通过选择合适的模式，用户可以控制泵速，以实现可变泵速或最大泵速。泵体积小且高效。Mk3 24V版本现在可设定最大转速为 $1.8 \text{ m}^3 \cdot \text{s}^{-1}$ ，转速为2400转/分钟。

在正常情况下，XDD1几乎无需维护，隔膜和阀门的使用寿命通常 $>10,000$ 小时，具体取决于应用。

XDD1 Mk2 是 XDD1 的第二代。它是市电驱动版本，提供广泛的电压供电范围，适用于全球范围。

## 产品特点

干式泵送、无润滑剂技术——免除了昂贵的换油和处理。


轻便紧凑——体积小，使用灵活。

理想的备份泵——适用于小型涡轮分子泵。

符合 EN61010、EN1012、CSA/UL标准。

全球范围内——115/230 V 或 24 V 可选。

IEC 60320 C13连接器——用于交流泵。



# 24小时为客户提供服务

高效率

高品质

高服务

除了拥有出色的性能、效率及实用性的真空设备，我们也可以提供精湛的服务和支持。无论是在我们的服务中心还是您的现场，我们均可为多个品牌和应用提供服务。可以快速响应您的需求，就算是不间断工艺，也可让您安心生产。

In addition to vacuum equipment with excellent performance, efficiency, and practicality, we can also provide exquisite servicesService and support. Whether in our service center or on your site, we can serve multiple brands and applicationsProvide services. We can quickly respond to your needs, even with uninterrupted processes, allowing you to produce with peace of mind.

## 你想了解更多吗？

请直接联系我们！

电话：185-6656-3069

邮箱：xiamu@boshanvac.com



在线客服



营业联系